



We designed the Macedonia Space Divider in order to create the most flexibility and freedom when dividing interior and exterior spaces. The system creates a highly decorative 3D effect, it is modular and very easy to install

Designed by *Fame*

Macedonia Space Divider



Especially when you install the Macedonia Space Divider both inside and outside, you can create the most fascinating design combinations



Due to its decorative design, this system can be used as part of the interiors of the highest nature in hotels and private residences




In order to divide spaces in offices where transparency and openness is required, the Macedonia Space Divider system is a perfect system




Bijenkorf department store in cooperation with Qua associates: double layer of warm grey Macedonia panels inside two sheets of glass

Macedonia Space Divider

DIMENSIONS



EXPLODED VIEW WITH U-PROFILE



PRODUCT INFORMATION

Type	Space divider for professional use
Designer	Janne Kyttänen 2010
Color	All RAL-colors are possible
Weight	630 grams per panel
Delivery time	4 weeks

MATERIAL

Glass filled polypropylene, or other thermoplastics such as ABS or polycarbonate. Fire retardant thermoplastics are also an option for spaces where this is required.

FINISH

Surface finish is very smooth in order to protect it from dust and dirt and also make very easy to clean. Due to each application being custom fitted to interior and exterior architectural solutions, practically any surface treatment can be applied such as flocking or gold plating.

CONNECTION SYSTEM

2 tripod units connected with a screw that holds the panels together. A little round cap is provided to cover the screw

INSTALLATION INSTRUCTION

At first instance this product is created for professional interior and exterior designs. Freedom Of Creation delivers the system as individual panels which can be easily assembled with just a screwdriver. In order to fit the panels in square surfaces, they need to be cut to size. The railings where it is mounted on are always tailor made and need to be fitted on location. The recommended dimensions of the U-profile railing are 40 x 40 x 3 mm. The internal width should be at least 34 mm in order to accommodate the panels.

Freedom Of Creation has the expertise to assist with installation and gives design advice for each situation. Please contact us with regards to your requirements.

DAILY USE INSTRUCTION

Due to the surface of the panels being smooth and non porous, they are easily cleanable with standard cleaning detergents. The panels are very modular and easy to mount and unmount. This makes the system ideal for not just permanent solutions, but also for temporary situations. Should any damage happen to the panels due to havok or other accidents, even single panels are easily replaced.

CUSTOM SOLUTIONS

Due to the system being custom fitted for each application, there are a number of ways to also customize the system for different spaces. For example hanging it on the wall, build inside glass panels or using multi-layer in order to play with translucency and colors. In order to create the most intriguing 3 dimensional shapes we are able to warp the structures around any double curved surface by use of 3D printing. By doing this, you are able to create innovative hybrid solutions by combining injection molded flat panels with curved 3D printed panels.

If you have such a custom application in mind, contact Freedom Of Creation for more details.